



Neonatal Feeding

Australian hospitals now have the choice of sterile PET or PE bottles with easy to read graduated scales.

PET bottles are highly transparent, readily recyclable and a barrier to gases

PE bottles can be used with boiling water

Our bottles are designed for EBM collection, storage or formula makeup and feeding.

Slow and Extra Slow flow silicon teats are available together with our bottles or individually packed.

All **Hodei** products are free of latex and the plastic additives Diethylhexyl-phthalate (DEHP) and Bisphenol A (BPA).



Item Code	Description	Carton Qty
F150	150ml sterile PET bottle	200
F150TXS	150ml sterile PET bottle and extra slow teat	200
E100	100ml sterile HDPE bottle	300
E150	150ml sterile HDPE bottle	200
E150TXS	150ml sterile HDPE bottle and extra slow teat	200
E250	250ml sterile HDPE bottle	160
E250TS	250ml sterile HDPE bottle and slow flow teat	160
TXS	Extra slow flow, sterile teat	144
TS	Slow flow, sterile teat	144
TXSSC	Extra slow flow teat & cap, sterile	100
TSSC	Slow flow teat & cap, sterile	100